



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Bio-Chemistry Analyzer, Automatic

Product Image



Description

Catalog No : 100143

Bio-Chemistry Analyzer, Automatic - Model 1201

SALIENT FEATURES

- ✓ Highly Stable and accurate
- ✓ Absorbance Range upto 3.000
- ✓ Range Selection Automatic Via Filter Wheel
- ✓ Inbuilt Thermal Printer
- ✓ Up to 300 test parameters
- ✓ Storage of 2,00,000 test results with patient information

TECHNICAL SPECIFICATIONS

Test Method	End Point With Standard/Factor Two Point Kinetics (Fixed Time) Multipoint Kinetics Multi standard up to 8 standards Biochromatic, Dual Wavelength Absorbance Coagulation
Optical System	Principle: Photometric Analysis with Interference Filter Absorbance Range: 0.0000-3.0000 (Linearity: $\pm 1\%$, Repeatability: 0.001, Resolution: 0.0001) Spectral Range Selection: Automatic Via Filter Wheel Wavelengths: 340, 405, 450, 505, 546, 578, 630 nm + 2 Free Positions, ± 2 CML Precision Light Source: 6 V 10 W Long Life tungsten Halogen Lamp Detector: Photodiode
Thermal System	Peltier Regulated 25°C, 30°C, 37°C & Room Temperature Accuracy: $\pm 0.3^\circ\text{C}$
Cuvettes	Flow Cell: Quartz 32 μl Path Length: 10 mm Removable Cuvette (Square and round)
Printer	Inbuilt Thermal Printer (57mm) Optional External Printer
Display & Input System	7.0 inch color touch screen External Keyboard, Mouse facility
Suction System	Pressure Auto releasing Peristaltic Pump Suction Volume: 300 μl to 3.0 ml Air Column facility after each sample to avoid carry over.

Test Parameter, Storage & CPU	Test Parameters: Up to 300 2,00,000 test results with editable patient information Storage of Quality Control And standard results DDR2 SDRAM: 1 G bit Flash: 256 MB ARM Cortex A8, 720 Mhz
Quality Control	Leu-Jennings Chart Using Westgard's Rule Auto Drawing of QC figures
Operating Conditions	Temperature: 10°C~37°C Relative Humidity: <85%
Power Requirement	Voltage: 100-240 V AC (Auto Adaption)
Dimensions	Frequency: 50/60 HZ External Power Adaptor: 19 V 4.7 Amp Dimensions: 400X300X160 (L*W*H) Weight: 6 Kg

ACCESSORIES

- Printer Paper Roll
- Removable Cuvette
- Optical Mouse
- External Key Board
- AC Adapter

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.