



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Colorimeter, Digital

Product Image



Description

8 Filters

1 ml solution measurements.

Standard glass filters.

Highly stable & accurate.

Technical Specification Std. Glass Filter: 8

Mini Volume: 1ml

Display: 2½ Digit LED

Range: 400-700 nm
Output: OD (0 to 1.99)
Resolution: OD: 0.01
Accuracy: 0.5% FSI
Detector: Selenium photocell
Light Source: 6.8V, 300mA
Power: 230V± 10% and in-built battery
Filters: 400, 420, 480, 500, 520, 540, 620, 680 nm

Accessories:

Set of 5 test tube.
Spare lamp.
Dust cover.
Manual.

Catalog No.	Particulars
JZ00590	Colorimeter, Digital

A quality product from JAPSON ideal for use in School Laboratories in developing countries of Asia, Africa and South America.

Standard specifications for school laboratory use. Ideal mix of Quality and Economy. Other configurations and superior quality available for specific use or for developed countries.

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.