



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Decade Resistance Box, Dial Type

Product Image



Description

These units employ high stability metal film resistance element having superior characteristics to traditional wire wound coils. Its equally suitable for AC or DC use. The individual decade are series connected in two dials, Three dials & four dials. We use high stability 1 percent carbon metal film resistance. Also available with Constantan or Manganin wound coil resistance for higher accuracy.

Catalog No.	Particulars
JP13160	Decade Resistance Box, Dial Type, Single Dial
JP13161	Decade Resistance Box, Dial Type, Two Dial
JP13162	Decade Resistance Box, Dial Type, Three Dial
JP13163	Decade Resistance Box, Dial Type, Four Dial

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.