



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# Dessicator (Vaccum), Plastic

## Product Image



## Description

---

**Material:** Polypropylene/ Polycarbonate

Dessicators are made of Polypropylene and Polycarbonate.. These autoclaveable vacuum dessicators can hold vacuum upto 740mm of Hg for 24hrs. Without and greasing. The top dome, moulded in rigid and transparent Polycarbonate, gives a crystal clear view of the desiccant placed inside. The Knurled knob on the top provides easy handling of the dome. The lower part is made of Polypropylene. An internal groove is provided on the flange to hold a silicon rubber O ring. The Polypropylene stopcock is fitted with a self lubricating PTFE plug. This plug works three way i.e. vacuum creation, shutting off & vacuum releasing.

Size (mm)	Catalog No.	Flange O.D.(mm)	I.D.(mm)
150	JW03201	171	150
200	JW03202	232	199
250	JW03203	276	240
300	JW03204	340	300

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.