



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Digital Automatic Polarimeter, Regular

Product Image



Description

Catalog No : 100136

Digital Automatic Polarimeter, Regular - Model 740

SALIENT FEATURES

- ✓ Micro processor Based
- ✓ User Friendly and menu driven software
- ✓ 128 x 64 Graphical LCD
- ✓ Two point calibration.
- ✓ USB Interface
- ✓ USB Port for interfacing the system with PC.
- ✓ One can see the stored logs on the system before printing
- ✓ Internal storage capacity of 1000 logs with date and time

TECHNICAL SPECIFICATIONS

- | | |
|-------------------------|--|
| ✓ Measuring Range | +/- 200° (Sugar Scale) +/- 70°
(optical rotation) |
| ✓ Accuracy | +/- 1° (Full Scale) |
| ✓ Resolution | 0.01° |
| ✓ Display | Graphical LCD (128 x 64) |
| ✓ Keys | 4-Keys for Menu Operation |
| ✓ Calibration Mode | 2 Point (zero & span) |
| ✓ Interface | USB |
| ✓ RTC | In-built clock with date and time display |
| ✓ Data Storage capacity | 1000 Logs with Date & Time |
| ✓ Power Supply | 230VAC +/- 10 %, 50Hz |

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.