



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Digital Automatic Polarimeter, Touch Screen

Product Image



Description

Catalog No. 100799

Digital Automatic Polarimeter, Touch Screen - Model 7510

TECHNICAL SPECIFICATIONS

4 Test modes	Optical rotation, specific rotation, sugar degree and concentration
Light source	LED
Measurement range	$\pm 45^\circ$ (optical rotation) $\pm 120^\circ$ Z(sugar)
Wavelength	589.3nm
Minimum indicating value	0.001° (optical rotation)
Accuracy	a) $\pm 0.01^\circ$ ($-15^\circ < \text{optical rotation} < +15^\circ$) b) $\pm 0.02^\circ$ (optical rotation $< -15^\circ$ or optical rotation $> +15^\circ$) Repeatability 0.002° (optical rotation)
Display	Color Touch Screen
Test tube	200mm, 100mm
Sample transmittance	$> 1\%$
Interface	USB & Rs232
Operation voltage	220V \pm 22V, 50Hz
Overall Dimensions	850mm x 500mm x 470mm
Weight(Gross)	38kg
Software	Yes

SALIENT FEATURES

- ✓ Touch Screen Colour Display
- ✓ Temperature Display
- ✓ Measurement of dark-colored sample
- ✓ USB & RS232
- ✓ No warm-up time is required when instrument is switched on
- ✓ Insulated Sample chamber to keep sample temp. constant
- ✓ Photodiode Detector

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.