



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Digital Conductivity Meter (Auto Ranging)

Product Image



Description

Catalog No : 100098

Digital Conductivity Meter (Auto Ranging) - Model 16

TECHNICAL SPECIFICATIONS

✓ DISPLAY	3½ Digit LED
✓ MEASUREMENT	Conductivity
✓ COND. RANGES	Five Ranges
✓ RANGE SELECTION	Automatic in 5 Ranges
✓ TEMP. RANGE	-5 to 110°C
✓ ACCURACY	
COND.	±0.5 % FS ± 1Digit
TEMP.	±0.1°C ± 1Digit
✓ TEMPERATURE COMPENSATION	Auto: 0 to 50 °C (in Model LT-26 Only) Manual: 0 to 50 °C in (Model LT-16)
✓ CELL CONSTANT	Adjustable on Digital Display
✓ MEASURING CELL	Platinum DIP Type
✓ CELL CONST. MEASUREMENT	Auto
✓ POWER	230V± 10% AC
✓ DIMENSIONS	270x202x80 mm (lxbxh)
✓ WEIGHT	0.8 Kg approx.
✓ ACCESSORIES	Conductivity Cell, Operation Manual, Dust Cover, Cell Stand, Temperature Probe (with models LT-26)

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.