



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# Digital Conductivity Meter (Auto Ranging)

## Product Image



## Description

Catalog No : 100098

Digital Conductivity Meter (Auto Ranging) - Model 16

## TECHNICAL SPECIFICATIONS

✓ DISPLAY	3½ Digit LED
✓ MEASUREMENT	Conductivity
✓ COND. RANGES	Five Ranges
✓ RANGE SELECTION	Automatic in 5 Ranges
✓ TEMP. RANGE	-5 to 110°C
✓ ACCURACY	
COND.	±0.5 % FS ± 1Digit
TEMP.	±0.1°C ± 1Digit
✓ TEMPERATURE COMPENSATION	Auto: 0 to 50 °C (in Model LT-26 Only) Manual: 0 to 50 °C in (Model LT-16)
✓ CELL CONSTANT	Adjustable on Digital Display
✓ MEASURING CELL	Platinum DIP Type
✓ CELL CONST. MEASUREMENT	Auto
✓ POWER	230V± 10% AC
✓ DIMENSIONS	270x202x80 mm (lxbxh)
✓ WEIGHT	0.8 Kg approx.
✓ ACCESSORIES	Conductivity Cell, Operation Manual, Dust Cover, Cell Stand, Temperature Probe (with models LT-26)

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.