



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Digital Fully Automatic Colorimeter

Product Image



Description

Catalog No. : 100149

Digital Fully Automatic Colorimeter - Model 116

Set of Test tube - 6 No.

TECHNICAL SPECIFICATIONS

✓ Range	400-700nm
✓ Display	Dual Digital Display
✓ Filters	Built-in 9 Digital filters > 30000 Hours Life
✓ Filters Wavelength	400nm, 430nm, 500nm, 520nm, 540nm, 580nm, 600nm, 620nm, 680nm
✓ Display Mode	Absorbance & Wavelength
✓ Detector	Silicon photo diode
✗ ✓ Zero Adjustment	Auto zero by microprocessor
✓ Accuracy	± 0.01 O.D.
✓ Stability	± 0.02 O.D. Per Hour
✓ Light Source	Highly Accurate Laser Source
✓ Amplifier	Micro Controller Based
✓ Volume	1 mL Minimum
✓ Dimension	L 210 X B 160 X H 80 mm (Approx)
✓ Weight	1.5 Kgs. (Approx)
✓ Power	230V ± 10% AC, 50 Hz,
✓ Battery Backup	6V Ni-Cd Re-Chargeable Battery
✓ Accessories	Set of Test Tube - 6 Nos, Dust Cover - 1 No, Operational Manual

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.