



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Digital Multimeter 2

Product Image



Description

Specification:

- 1. Display: 3-1/2 digits LCD with a maximum reading of 1999.
 - 2. Measurement rate: updates 2-3 sec.
 - 3. Over range indication: "1" figure only in the display
 - 4. Automatic negative polarity indication.
 - 5. The " " displayed when the battery voltage drops below the operating voltage.
 - 6. Full range over load protection.
 - 7. Capacitance measurement Auto-Zeroing.
 - 8. Auto Power Off It will be automatically cut off in about 15 minutes after the power is turned on. It needs to be turned off and turned on again to continue the power.
 - 9. Operating temperature: 0°C~40°C, 0~75% R.H. Storage temperature: -10°C~50°C, 0~75% R.H.
 - 10. Power Single standard 9V battery EC 6F22, NEDA 1604, JIS 006P.
 - 11. Dimensions: 191L*89W*35Hmm.
 - 12. Weight: approx. 310g (including battery)
 - 13. Accessories: test leads (pair), spare fuse 0.5A piece in case (model DT9201A fuse 2A), K-type thermocouple wire (model DT9207A/DT9208A only), and operator's manual.
3. ELECTRICAL SPECIFICATIONS Accuracy is given as \pm (% of reading + number of least significant digits) for one year, at 23°C \pm 5°C RH< 75.

-

Catalog No.	Particulars
DT9201A	Digital multimeter 2

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.