



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Disintegrator Motor

Product Image



Description

The Motor is Laboratory size, Harmer type, with $\frac{1}{4}$ H.P. heavy duty motor (single phase) 220 volts, A.C. Consisting of three steel hammers fixed to a disc of 3" in diameter 1" thick, through which passes a shaft being revolved at 3000 R.P.M. The hammers are enclosed in a C.I. Drum, the sides & upper surface of which are roughened. The inner screen (sieves) of different mesh size a set of three sieves of 20,40,60 mesh. Hopper is made of heavy aluminum sheet built on angle iron frame.

Capacity : 4-5 Kg Per Hour

-

Disintegrator Motor

Catalog No. 100640

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.