



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# Galvanometer, EDSPOT

## Product Image



## Description

---

Consist of an integral taut suspension movement, lamp unit and scale, the indication being presented as a hairline in a brilliant light spot on a translucent screen. Provision for effectively damping any transverse suspension vibrations, without affecting the electrical characteristics of the instrument. 4mm colour coded socket terminals is provided with signal input. With Lock/Unlock, zero adjustment and sensitivity adjustment at the front. Front scale: Graduated in millimeters from 0-18cm (left zero) and 9-0-9cm (center zero) Input Mains: 220-240C AC mains, 50/60Hz.

Range attenuation - sensitivities of x1, x0.1, x0.01 and x0.001, related to both current and voltage sensitivities with constant input resistance.

<b>Catalog No.</b>	<b>Model</b>
JP11460	Galvanometer, EDSPOT

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.