



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Glass Drying Oven, Double Door

Product Image



Description

These are manufactured using high-quality materials and cutting-edge technologies. Our goods are widely regarded for their high quality and extended lifespan. These are offered at

industry-leading prices. They are made of coated mild steel on the outside and stainless steel on the inside, making them both sturdy and corrosion-resistant.

It can set and save the operating temperature, humidity reduction temperature, humidity reduction duration, temperature holding time, and shutdown temperature, after which the Sterilization Drying Oven will automatically carry out all operations according to the established protocols.

Drying ovens can be used in laboratories or industries for several purposes such as evaporation, sterilizing, temperature testing, and incubating temperature-sensitive studies. A drying oven is designed to eliminate moisture from the oven chamber as rapidly as possible to dry the samples.

-

Glass Drying Oven, Double Door

Catalog No. 101279

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.