



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Gooseneck Arm Quartz Halogen Lamp

Product Image



Description

Gooseneck Arm Quartz Halogen Lamp contains an engineering plastic shade and the base provides complete insulation for maximum safety of the operator. The articulate arm provides vibration resistant performance. It operates on 20 watt or 50 watt, 220 volt AC. The transformer is built in the base. The lamp is available with length of the gooseneck equal to 700mm. The Quartz Halogen Lamp provides very good light output which is soft illuminating without irritating to the eyes. The equipment is ideally suited to machine tools and machinery without big work area.

Lamp Head Diameter: 74mm

Model	Catalog No.
Gooseneck Arm Quartz Halogen Lamp	JH-20FT

Note: Halogen machine lights are also offered in 12V / 24V operation, depending on the quantity.

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.