



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Grain Moisture Meter

Product Image



Description

Features:

--

Grain moisture meter quickly measures both grain temperature and moisture. It is suitable for food allocation, processing and storage. The Gm640 is capable to measure 8 grain species, which includes paddy, wheat, barley, forage, corn, rapeseed, soybean, rice.

Specifications		
Measuring Range	Moisture: 5%-30%,	Temperature:-10°C-60°C
Accuracy	Moisture $\pm(1\%rh+0.5)$,	Temperature: $\pm 2.5^{\circ}C(5^{\circ}F)$
Resolution	Moesture: 0.5%,	Temperature:0.1°C/0.1°F
Opert. Environment	Temperature:0°C-40°C,	Humidity: 0~-85%RH
Auto Power Off	5 minutes without Any Operation	
Unit Size	Host device: 72*35*145mm,	Probe: 415*36*36mm
Weight	Host device: 190.6g,	Probe: 208.3g
Power	3*1.5V AAA Batteries	

--

Grain Moisture MeterCatalog No. 101422

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.