



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# High Vibration Resistant Quartz Halogen Lamp

## Product Image



## Description

---

The equipment can be operated on 220 volt operation without the danger of electric shock. The Quartz Halogen lamps are particularly suited to machine and inspection applications in demanding environments. The articulate arm of the lamp provides vibration resistant performance.

High Vibration Resistant Quartz Halogen Lamp works on 20 watt or 50 watt, 220 volt AC power. The luminaire head can rotate though an angle of 250 deg. It is available in two options namely JH-20RTM (Medium arm), JH-20RTL (Long arm). Lamp Head Diameter: 72 mm

**Arm Length**  
20RTM 440 mm  
20RTL 800 mm

Model	Catalog No.
High Vibration Resistant Quartz Halogen Lamp	JH-20RTL
High Vibration Resistant Quartz Halogen Lamp	JH-20RTM

**Note:** Halogen machine lights are also offered in 12V / 24V operation, depending on the quantity.

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.