



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Ice Flaker

Product Image



Description

Salient Features

- ✦ Fully Automatic microprocessor control
- ✦ Stainless Steel construction
- ✦ Continuous Ice Flakes Output
- ✦ CFC free compressor
- ✦ Low water level Indication
- ✦ Overload protection
- ✦ Noiseless operation
- ✦ Compact Design and low maintenance

APPLICATION :

Hospitals, Educational Research Institutes &
Biotechnology Laboratories

SPECIFICATIONS	MODEL	LMIF30	LMIF50	LMIF100
	Capacity of Ice flake (kg per 24 hrs.)	30 kg	50 kg	100 kg
	Storage Capacity (kg ~ app.)	5 kg	7 kg	15 kg
	Storage bin	ABS Plastic		
	Cooling Method	Air		
	Ambient temperature	Below 25 °C for optimum working		
	Construction	Stainless Steel		
	Noise level	≤52 dB		
	Water Supply	3 / 4 inch BSP		
	Refrigerant	R134A		
	Input Power	180W	280W	420W
	Power supply	AC 220V / 50Hz		
	Dimension LxWxH (mm)	300X493X547	380X543X722	548X611X883
	Gross Weight	36kg	45kg	64kg

Please use Ice Flaker with stabilizer for better result

Ice Flaker

Catalog No. 101120

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.