



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

---

# Ice Flaker

## Product Image

---



## Description

---

## *Salient Features*

- ◆ Fully Automatic microprocessor control
- ◆ Stainless Steel construction
- ◆ Continuous Ice Flakes Output
- ◆ CFC free compressor
- ◆ Low water level Indication
- ◆ Overload protection
- ◆ Noiseless operation
- ◆ Compact Design and low maintenance

### APPLICATION :

Hospitals, Educational Research Institutes & Biotechnology Laboratories

MODEL	LMIF30	LMIF50	LMIF100
Capacity of Ice flake (kg per 24 hrs.)	30 kg	50 kg	100 kg
Storage Capacity (kg ~ app.)	5 kg	7 kg	15 kg
Storage bin	ABS Plastic		
Cooling Method	Air		
Ambient temperature	Below 25 °C for optimum working		
Construction	Stainless Steel		
Noise level	≤52 dB		
Water Supply	3 / 4 inch BSP		
Refrigerant	R134A		
Input Power	180W	280W	420W
Power supply	AC 220V / 50Hz		
Dimension LxWxH (mm)	300X493X547	380X543X722	548X611X883
Gross Weight	36kg	45kg	64kg

Please use Ice Flaker with stabilizer for better result

Ice Flaker

**Catalog No. 101120**

## Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.