



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Industrial Crane Scale

Product Image



Description

Features :

1. High strength rotary hook, 360 swivel rotating hook, weigh up the weight after rotation. (For up to 10T Capacity Only)
2. 5 Digit 30mm LED display visual> 25 meters.
3. Switch on/off the scale automatically displays the charge voltage of Battery.
4. RF-Remote for easy operation.
5. Two Re-Chargable Batteries for continues use one by one.
6. The main board design low energy consumption and prolong the using time.
7. The unique only charging protection, prevent over-current, overcharge, the battery service life is stronger, more durable.
8. Alarm overload, low voltage, the voltage is less than 5.5 v when prompted.
9. Function: 29 Auto Save Memories for Last Weighment Record. HOLD Last Weight, TARE & ZERO.

MODEL	CAPACITY (M.T.)	RESOLUTION (KG)	REPEATABILITY (KG)	DISPLAY	MOC
500k	0.5t	0.1kg	0.2	LCD	ABS PLASTIC
1T	1t	0.2kg	0.5	1" LED	Mild Steel
2T	2t	0.5kg	1	1.2" LED	Alum. Die-Cast
3T	3t	0.5kg	1	1.2" LED	Alum. Die-Cast
5T	5t	1kg	2	1.2" LED	Alum. Die-Cast
10T	10t	2kg	5	1.2" LED	Alum. Die-Cast
15T	15t	5kg	10	1.2" LED	Alum. Die-Cast
20T	20t	5kg	15	1.5" LED	Mild Steel
30T	30t	10kg	20	1.5" LED	Mild Steel
50T	50t	20kg	50	2" LED	Mild Steel

-500K do not have re-chargeble battery option & RF-Remote. Display Type : 20mm LCD

-1T do has only one re-chargeble battery option.

Optional Accessories



Wireless Display



Printer



Wireless Indicator

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.