



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Industrial Inspection Microscope, Metallurgical

Product Image



Description

1. Big stage with extra large moving range 250x250mm.
2. Well designed structure, easy to operate. It is specially used in IT industry for large area integrated circuit, wafer observation and inspection.
3. Excellent optical quality with infinite optical system and LWD high magnification objective (40X/WD 3.7mm)
4. Stage speedy movement by hand to get observation point immediately.
5. Comfortable and enjoyable operation with low and pre position control knob.
6. Suitable for different specimen observation with polarization set.
7. Easy, safe and reliable lamp replacement device.
8. Available for measuring with digital camera and software.

Body:	Trinocular head with quadruple nosepiece.
Stage:	300x268mm/ 250x250mm.
Focussing:	Coaxial fine & coarse adjustment range 24mm.
Illumination:	6V/ 20W halogen lamp, brightness adjustable.
Eyepiece:	Extra wide field eyepiece EW10X/ 22.
Objective:	Infinitive plan achromatic objectives.
	4X / 0.1 WD 25.4mm 10X / 0.25 WD 11mm 20X / 0.4 WD 6mm 40X / 0.6 WD 3.7mm
Filters:	Blue, Green, Yellow & Ground Glass.
Box:	Supplied in hard packing.

Model	Catalog No.
Industrial Inspection Microscope, Metallurgical	JM006200

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.