



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

---

# Laser Distance Meter

## Product Image

---



## Description

---

Features:

--

## Features

- ❖ The Max Measurement Range 40/60/80/100 Meter
- ❖ When in less Reflect Light, please use Sight Vane
- ❖ The Surface of the Measured Object
- ❖ It will make mistakes if the Surface of the Object is Liquid(water) or clear Transparent Surface
- ❖ When measure no Reflected or Dark Surface, it will increase the Measuring Time Storage
- ❖ It's for bidden to place the meter into water, please uses soft and damp cloth to clean the meter, don't use corrosion or volatilization to clean it

## Specifications

	40m	60m	80m	100m
Measuring	0.05-40M	0.05-60M	0.05-80M	0.05-100M
Accuracy	+/-1.5mm		Back Light	Yes
Measurement Unit	Mm/in/ft		Beep Display	Yes
Memory Data Hold	Last 20 Data Stored		Continuous Measurement	Yes
Laser Point Diameter	8/40mm		Outdoor Target Reflection Board	Yes
Power	2*1.5VAA		Area/Volume Calculations	Yes
Power Life	5,000 Times		Measurement using Pythagoras	Yes
Storage Temperature	25°C to 70°C (13°F to 158°F)		Addition/Subtraction	Yes
Operating Temperature	10°C to 50°C (14°F to 122°F)		Min/Max Measurement	Yes
Weight / Dimension	100g / 116*56*32mm		Laser Level	Class II
Laser Type	635nm, <1mW		Auto Laser Off	30s
Located Position	(10/60m)			

--  
Laser Distance Meter

Catalog No. **101420**

## Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.