



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Micro Centrifuge, 16000 R.P.M.

Product Image



Description

Model : T-16

Specifications:

- High speed Micro Centrifuge Max. r.p.m. 16000 and r.c.f 16800.
- Heavy duty plastic injection moulded body.
- Stainless Steel protection bowl.
- Fitted with well balance universal motor having long life with high grade carbons.
- 2 lines of 16 character LCD display of r.p.m., r.c.f, set time and run time.
- Digital timer which can be set from 0-99 minutes in interval of 1 minute.
- Programmable Speed Regulator from 2000 to 16000 in variation of 100 rpm.
- Last test parameter recall and displays automatically on LCD.

Supply completed with following accessories:

- Rotor Head to accommodate 12 eppendorf/ Micro Centrifuge Tubes with cover of 1.5ml /2ml (12 x 1.5/2ml).
- Reduction adapters for 0.2/0.5ml eppendorf (Micro Centrifuge Tubes).
- Supply is complete with head Puller, Spanner, Instruction manual, Cord & plug to work on 220 volts 50Hz A.C.

Dimension of Machine:	L = 290mm, W = 270mm, H = 240mm
Weight of Machine:	9.5kg. approx.
Dimension of box:	L-355mm x W355 x H-340mm
Weight of Box	11 kg. approx.

Micro Centrifuge, 16000 R.P.M.

Catalog No. 100765

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.