



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Micro Centrifuge, Micro Processor Based, 16000 rpm

Product Image



Description

High speed Micro Centrifuge Max rpm 16000, Heavy duty plastic injection moulded body, Stainless Steel protection bowl, Fitted with well balance universal motor having long life with imported carbons, Microprocessor based Digital Timer of range 0-15 min. with LCD display, Preset speed controls thru microprocessor from 2000 to 16000rpm, Digital display shows Set Time/Run Time/rpm.

Special Features

Microprocessor based.

Fitted with anti vibration pads.

Motor remain cool even after running full time

See through acrylic lid.

Supply completed with following accessories :

Rotor Head to accommodate 12 eppendorf (Centrifuge Tubes with cover) of 1.5ml/2ml (12 x 1.5/2ml) .

Reduction adopters for 1.5ml eppendorf (Micro Centrifuge Tubes)

Head Puller, spanner, dust cover, instruction manual, cord & plug to work on 220 volts 50 Hz A.C.

Optional at extra cost:

Rotor head to accommodate 24 micro tubes

Any other size of rotor to accommodate micro-centrifuge can be supplied at customer requirement.

Model

Catalog No.

Micro Centrifuge, Digital, 13000
r.p.m

JA10200

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.