



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Moisture Analyzer - 60g/0.1mg

Product Image



Description

Salient Features

- ✦ Based on E.M.F.C. Technology
- ✦ Halogen Heating System
- ✦ Temperature Range upto 200°C
- ✦ RS232C Interface
- ✦ The mode for testing Automatic, Timing, Manual.

Moisture Analyzer based on E.M.F.C sensor and its working on the principle of thermal force. from the percentage between the weight when the sample is dry and the weight when the sample is moist. we can get the value of moisture.

SPECIFICATIONS	MODEL	HMB50H
	Capacity	60 g
	Readability	0.1 mg (0.005%)
	Display	LCD
	Range of Temperature	50°C - 200°C (Interval 1°C)
	Pan Size	90 mm Ø
	Testing Mode	Auto / Timing / Manual
	Content of Display	% Moisture, Time, Temperature, Weight
	Tare Range	Full
	Operating Temperature	10°C to 40°C
	Time Setting	1- 120 min interval : 1min
	Heating Source	Halogen Lamp
	Interface	RS232C
	Power Supply	AC 220V / 50-60Hz
	Dimension (LxWxH) mm	330 x 200 x 155
	Weight (app.)	5.5 kg

* 0.005% for very dry sample

Moisture Analyzer - 60g/0.1mg

Catalog No. 101135

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.