



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Moisture Analyzer 2, Axis Poland

Product Image



Description

Features :

1. Halogen heaters (Option: Infrared Type)
2. Drying temperature up to 160°C (Option 250°C)
3. Robust die-cast metal housing.
4. Graphical display with backlight & Drying chart displaying.
5. Convenient and Easy text menu.
6. Reports edition with PC keyboard.
7. Storing 20 drying programs.

8. Equipped with USB, RS232, PS2 Interface.
9. Free PC Software.
10. Multiple profiles and analysis modes.
11. Drying Report Printing with GLP/GMP.
12. Analysis Parameters Memory Bank.
13. Available ways to evaluate humidity:
 - in proportion to initial weight
 - in proportion to dried weight
 - percentage of dried weight
14. Drying mode:
 - time
 - short (automatic)

MODEL	60	120	210	60 T250	120 T250	120 IR	210 IR
CAPACITY [g]	60	120	210	60	120	120	210
RESOLUTION [g]	0.001	0.001	0.001	0.001	0.001	0.001	0.001
MOISTURE RESOLUTION [%]	0.01	0.01	0.01	0.01	0.01	0.01	0.01
DRYING MAX. TEMPERATURE	160°C			250°C		160°C	
HEATING TECHNOLOGY	HALOGEN					INFRARED	
PAN SIZE [mm]	∅ 90						
HUMIDITY MEASURE REPEATABILITY	± 0.1% (sample 2g) / ± 0,04% (sample 5g)						
HUMIDITY READOUT PRECISION	1% < 0.5g sample / 0.1% < 5g sample / 0.01% > 5g sample						

Optional Accessories



**Calibration
Thermometer**



Printer



Software



Test Weights

Moisture Analyzer 2, Axis Poland

Catalog No. 100305

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.