



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

---

# Moving Coil Meter, Rectangular Dial, Front Terminal, Superior, (Ammeters, Milli-Ammeters, Micro-Ammeters, Voltmeters and Galvanometer)

## Product Image

---



## Description

---

**Case:** Unbreakable, moulded, ABS Plastic Black Case with clear transparent front window.

**Accuracy:**  $\pm 2$  F.S.D.

**Scale Length:** 85mm (approx.) with knife edge pointer with or without anti parallax mirror scale

**Desk Stand:** Unbreakable ABS plastic black or white desk stand with 4mm terminal at the front.

**Packing:** Thermocol Box

### Ammeters

Catalog No.	Range
JP11300	0-1A
JP11301	0-1.5A
JP11302	0-3A
JP11303	0-5A
JP11304	0-10A
JP11305	0-15A
JP11306	0-20A
JP11307	0-25A
JP11308	0-30A

### Millivoltmeter

Catalog No.	Range
JP11360	0-25mV
JP11361	0-50mV
JP11362	0-100mV
JP11363	0-150mV
JP11364	0-250mV
JP11365	0-500mV

### Micro-Ammeters

Catalog No.	Range
-------------	-------

JP11320	0-25 $\mu$ A
JP11321	0-50 $\mu$ A
JP11322	0-100 $\mu$ A
JP11323	0-200 $\mu$ A
JP11324	0-250 $\mu$ A
JP11325	0-500 $\mu$ A
JP11326	0-1000 $\mu$ A

### **Ammeters, Dual Range**

<b>Catalog No.</b>	<b>Range</b>
JP11330	0-10/100mA
JP11331	0-25/250mA
JP11332	0-100/500mA
JP11333	0-2.5/5A
JP11335	0-1/5A
JP11336	0-5/10A
JP11337	0-10/20A

### **Ammeters, DC, Triple Range**

<b>Catalog No.</b>	<b>Range</b>
JP11340	0-10/100/500mA
JP11341	0-50mA/500mA/5A

### **Voltmeters**

<b>Catalog No.</b>	<b>Range</b>
JP11350	0-1V
JP11351	0-1.5V
JP11352	0-3V
JP11353	0-5V

JP11354	0-10V
JP11355	0-25V
JP11356	0-50V
JP11357	0-100V
JP11359	0-300V

### **Voltmeters, Dual Range**

<b>Catalog No.</b>	<b>Range</b>
JP11370	0-1/5V
JP11371	0-3/6V
JP11372	0-3/15V
JP11373	0-5/15V
JP11374	0-7.5/15V
JP11375	0-3/30V
JP11376	0-30/60V
JP11377	0-100/500mV
JP11378	0-250/500mV

### **Voltmeters, Triple Range**

<b>Catalog No.</b>	<b>Range</b>
JP11380	0-3V/15V/30V
JP11381	0-3V/30V/300V

### **Galvanometer**

<b>Catalog No.</b>	<b>Range</b>
JP11390	1-0-1mA
JP11391	35-0-35mV
JP11392	3.5-0-3.5mA
JP11393	30-0-30, sensitivity 200 $\mu$ A/division

**Note:** Custom range meters available on demand.

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.