



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Moving Coil Meter, Rectangular Dial, Front Terminal (Ammeters, Milli-Ammeters, Micro-Ammeters, Voltmeters and Galvanometer)

Product Image



Description

Case: Unbreakable, moulded, ABS Plastic Black Case with clear transparent front window.

Accuracy: ± 2 F.S.D.

Scale Length: 60mm (approx.) with knife edge pointer with or without anti parallax mirror scale

Desk Stand: Unbreakable ABS plastic black or white desk stand with 4mm terminal at the front.

Packing: Thermocol Box

Ammeters

Catalog No.	Range
JP11200	0-1A
JP11201	0-1.5A
JP11202	0-3A
JP11203	0-5A
JP11204	0-10A
JP11205	0-15A
JP11206	0-20A
JP11207	0-25A
JP11208	0-30A

Milli-Ammeters

Catalog No.	Range
JP11210	0-1mA
JP11211	0-5mA
JP11212	0-10mA
JP11213	0-25mA

JP11214	0-50mA
JP11215	0-100mA
JP11216	0-250mA
JP11217	0-500mA
JP11218	0-750mA

Micro-Ammeters

Catalog No.	Range
JP11220	0-25 μ A
JP11221	0-50 μ A
JP11222	0-100 μ A
JP11223	0-200 μ A
JP11224	0-250 μ A
JP11225	0-500 μ A
JP11226	0-1000 μ A

Ammeters, Dual Range

Catalog No.	Range
JP11230	0-10/100mA
JP11231	0-25/250mA
JP11232	0-100/500mA
JP11233	0-2.5/5A
JP11234	0-1/3A
JP11235	0-1/5A
JP11236	0-5/10A

JP11237 0-10/20A

Ammeters, DC, Triple Range

Catalog No.	Range
JP11240	0-10/100/500mA
JP11241	0-50mA/500mA/5A

Voltmeters

Catalog No.	Range
JP11250	0-1V
JP11251	0-1.5V
JP11252	0-3V
JP11253	0-5V
JP11254	0-10V
JP11255	0-25V
JP11256	0-50V
JP11257	0-100V
JP11258	0-250V
JP11259	0-300V

Millivoltmeter

Catalog No.	Range
JP11260	0-25mV
JP11261	0-50mV
JP11262	0-100mV

JP11263	0-150mV
JP11264	0-250mV
JP11265	0-500mV

Voltmeters, Dual Range

Catalog No.	Range
JP11270	0-1/5V
JP11271	0-3/6V
JP11272	0-3/15V
JP11273	0-5/15V
JP11274	0-7.5/15V
JP11275	0-3/30V
JP11276	0-30/60V
JP11277	0-100/500mV
JP11278	0-250/500mV

Voltmeters, Triple Range

Catalog No.	Range
JP11280	0-3V/15V/30V
JP11281	0-3V/30V/300V

Galvanometer

Catalog No.	Range
JP11290	1-0-1mA
JP11291	35-0-35mV

JP11292

3.5-0-3.5mA

JP11293

30-0-30, sensitivity 200 μ A/division

Note: Custom range meters available on demand.

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.