



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# Moving Coil Meter, Rectangular Dial, Front Terminal (Ammeters, Milli-Ammeters, Micro-Ammeters, Voltmeters and Galvanometer)

## Product Image



## Description

---

**Case:** Unbreakable, moulded, ABS Plastic Black Case with clear transparent front window.

**Accuracy:**  $\pm 2$  F.S.D.

**Scale Length:** 60mm (approx.) with knife edge pointer with or without anti parallax mirror scale

**Desk Stand:** Unbreakable ABS plastic black or white desk stand with 4mm terminal at the front.

**Packing:** Thermocol Box

### Ammeters

Catalog No.	Range
JP11200	0-1A
JP11201	0-1.5A
JP11202	0-3A
JP11203	0-5A
JP11204	0-10A
JP11205	0-15A
JP11206	0-20A
JP11207	0-25A
JP11208	0-30A

### Milli-Ammeters

Catalog No.	Range
JP11210	0-1mA
JP11211	0-5mA
JP11212	0-10mA
JP11213	0-25mA

JP11214	0-50mA
JP11215	0-100mA
JP11216	0-250mA
JP11217	0-500mA
JP11218	0-750mA

### **Micro-Ammeters**

<b>Catalog No.</b>	<b>Range</b>
JP11220	0-25 $\mu$ A
JP11221	0-50 $\mu$ A
JP11222	0-100 $\mu$ A
JP11223	0-200 $\mu$ A
JP11224	0-250 $\mu$ A
JP11225	0-500 $\mu$ A
JP11226	0-1000 $\mu$ A

### **Ammeters, Dual Range**

<b>Catalog No.</b>	<b>Range</b>
JP11230	0-10/100mA
JP11231	0-25/250mA
JP11232	0-100/500mA
JP11233	0-2.5/5A
JP11234	0-1/3A
JP11235	0-1/5A
JP11236	0-5/10A

JP11237 0-10/20A

### **Ammeters, DC, Triple Range**

<b>Catalog No.</b>	<b>Range</b>
JP11240	0-10/100/500mA
JP11241	0-50mA/500mA/5A

### **Voltmeters**

<b>Catalog No.</b>	<b>Range</b>
JP11250	0-1V
JP11251	0-1.5V
JP11252	0-3V
JP11253	0-5V
JP11254	0-10V
JP11255	0-25V
JP11256	0-50V
JP11257	0-100V
JP11258	0-250V
JP11259	0-300V

### **Millivoltmeter**

<b>Catalog No.</b>	<b>Range</b>
JP11260	0-25mV
JP11261	0-50mV
JP11262	0-100mV

JP11263	0-150mV
JP11264	0-250mV
JP11265	0-500mV

### **Voltmeters, Dual Range**

<b>Catalog No.</b>	<b>Range</b>
JP11270	0-1/5V
JP11271	0-3/6V
JP11272	0-3/15V
JP11273	0-5/15V
JP11274	0-7.5/15V
JP11275	0-3/30V
JP11276	0-30/60V
JP11277	0-100/500mV
JP11278	0-250/500mV

### **Voltmeters, Triple Range**

<b>Catalog No.</b>	<b>Range</b>
JP11280	0-3V/15V/30V
JP11281	0-3V/30V/300V

### **Galvanometer**

<b>Catalog No.</b>	<b>Range</b>
JP11290	1-0-1mA
JP11291	35-0-35mV

JP11292

3.5-0-3.5mA

JP11293

30-0-30, sensitivity 200 $\mu$ A/division

**Note:** Custom range meters available on demand.

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.