



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Moving Coil Meter, Round Dial, Front Terminal (Ammeters, Milli-Ammeters, Micro-Ammeters, Voltmeters and Galvanometer)

Product Image



Description

Case: Unbreakable, moulded, ABS Plastic Black Case.

Accuracy: ± 2 F.S.D.

Scale Length: 50mm (approx.) with knife edge pointer with or without anti parallax mirror scale

Desk Stand: Unbreakable ABS plastic black or white desk stand with 4mm terminal at the front.

Ammeters

Catalog No.	Range
JP11100	0-1A
JP11101	0-1.5A
JP11102	0-3A
JP11103	0-5A
JP11104	0-10A
JP11105	0-15A
JP11106	0-20A
JP11107	0-25A
JP11108	0-30A

Milli-Ammeters

Catalog No.	Range
JP11110	0-1mA
JP11111	0-5mA
JP11112	0-10mA
JP11113	0-25mA
JP11114	0-50mA

JP11115	0-100mA
JP11116	0-250mA
JP11117	0-500mA
JP11118	0-750mA

Micro-Ammeters

Catalog No.	Range
JP11120	0-25 μ A
JP11121	0-50 μ A
JP11122	0-100 μ A
JP11123	0-200 μ A
JP11124	0-250 μ A
JP11125	0-500 μ A
JP11126	0-1000 μ A

Ammeters, Dual Range

Catalog No.	Range
JP11130	0-10/100mA
JP11131	0-25/250mA
JP11132	0-100/500mA
JP11133	0-2.5/5A
JP11134	0-1/3A
JP11135	0-1/5A
JP11136	0-5/10A
JP11137	0-10/20A

Ammeters, DC, Triple Range

Catalog No.	Range
JP11140	0-10/100/500mA
JP11141	0-50mA/500mA/5A

Voltmeters

Catalog No.	Range
JP11150	0-1V
JP11151	0-1.5V
JP11152	0-3V
JP11153	0-5V
JP11154	0-10V
JP11155	0-25V
JP11156	0-50V
JP11157	0-100V
JP11158	0-250V
JP11159	0-300V

Millivoltmeter

Catalog No.	Range
JP11160	0-25mV
JP11161	0-50mV
JP11162	0-100mV
JP11163	0-150mV

JP11164 0-250mV

JP11165 0-500mV

Voltmeters, Dual Range

Catalog No.	Range
JP11170	0-1/5V
JP11171	0-3/6V
JP11172	0-3/15V
JP11173	0-5/15V
JP11174	0-7.5/15V
JP11175	0-3/30V
JP11176	0-30/60V
JP11177	0-100/500mV
JP11178	0-250/500mV

Voltmeters, Triple Range

Catalog No.	Range
JP11180	0-3V/15V/30V
JP11181	0-3V/30V/300V

Galvanometer

Catalog No.	Range
JP11190	1-0-1mV
JP11191	35-0-35mV
JP11192	3.5-0-3.5mA

JP11193

30-0-30, sensitivity 200 μ A/division

Note: Custom range meters available on demand.

Note: Please give your choice of Black and White case at the time of order.

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.