



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Multirange Meter

Product Image



Description

Multirange Ammeter & Voltmeter are designed for schools & colleges to measure voltage & current in a DC circuit.

Measuring Range:

Current: 0- 100 μ A- 100 mA- 1A-5A

Voltage: 0-100 mV- 1V- 10V- 50V

Accuracy: ± 2.5 FSD

Dimensions: 162x114x60 mm (approx)

Scale Length: 60mm (approx)

Weight: 400 gm (approx)

| Catalog No. | Model |
|-------------|------------------|
| JP11420 | Multirange Meter |

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.