



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Multirange Meter

Product Image



Description

Multirange Ammeter & Voltmeter are designed for schools & colleges to measure voltage & current in a DC circuit.

Measuring Range:

Current: 0- 100 μ A- 100 mA- 1A-5A

Voltage: 0-100 mV- 1V- 10V- 50V

Accuracy: \pm 2.5 FSD

Dimensions: 162x114x60 mm (approx)

Scale Length: 60mm (approx)

Weight: 400 gm (approx)

Catalog No.	Model
JP11420	Multirange Meter

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.