



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Osilloscope, Dual Channel

Product Image



Description

Cathode ray oscilloscope is an electronic test equipment that primarily consists of a cathode ray tube, a vertical & horizontal amplifier, a time base and a power supply.

Specification:

Width of band: DC (AC 10Hz) ~20MHz

Max. Input Voltage: 400V (DC + AC peak) at 1KHz

Input Impedance: $1\text{M}\Omega \pm 5\%$ $25\text{pF} \pm 5\text{pF}$

-

Catalog No.

Particulars

ADSO102

Osilloscope, Dual Channel, 20 MHz

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.