



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Oven, Hot Air, Memmert Type, Stainless Steel, PID Controller with Fan

Product Image



Description

Hot air ovens are suitable for temperature up to 250°C for chemicals, glassware in laboratories, research institutions, industries, hospitals & R & D centers. They are used in various applications like heating, drying, sterilizing & baking.

Construction : All external cases are made of mild steel, with strong seamless welding & covered with a thick layer of stoved epoxy polyster paint. This provide a strong, highly screech & heat resistant surface for a long lasting attractive finish. Internal surfaces (including the doors) are manufactured from stainless steel, with great care in order to eliminate sharp edges. The double walled chamber is filled with high grade insulation to prevent heat loss. Elements are of the sheathed black type. They are put inside beads, placed at the bottom & in both the side ribs for uniform temperature. The door closes on to an asbestos-gasket. The shelves slide neatly into the fixed runners. The fixed ventilators are provided on both sides of the wall. The oven is mounted on four rubber feet to prevent slipping. The control panel houses a main On/Off switch & indicator lamp. Oven is provided with P.I.D. based controller for more precise control. Provided with circulating fan for achieving uniform temperature throughout the chamber.

Particulars	Catalog No.
Oven, Hot Air, Memmert Type, Stainless Steel, PID Controller with Fan, 355 x 355 x 355mm, 800 watts, 45 litre, 2 shelves	JA22071
Oven, Hot Air, Memmert Type, Stainless Steel, PID Controller with Fan, 405 x 405 x 405mm, 1000 watts, 65 litre, 2 shelves	JA22072
Oven, Hot Air, Memmert Type, Stainless Steel, PID Controller with Fan, 455 x 455 x 455mm, 1500 watts, 95 litre, 2 shelves	JA22073
Oven, Hot Air, Memmert Type, Stainless Steel, PID Controller with Fan, 455 x 455 x 605mm, 2000 watts, 125 litre, 2 shelves	JA22074
Oven, Hot Air, Memmert Type, Stainless Steel, PID Controller with Fan, 605 x 605 x 605mm, 2000 watts, 220 litre, 2 shelves	JA22075
Oven, Hot Air, Memmert Type, Stainless Steel, PID Controller with Fan, 605 x 605 x 910mm, 3000 watts, 330 litre, 3 shelves	JA22076

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.