



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# Oven, Hot Air, Memmert Type, Stainless Steel, Thermostatic with Fan

## Product Image



## Description

---

Hot air ovens are suitable for temperature up to 250°C for chemicals, glassware in laboratories, research institutions, industries, hospitals & R & D centers. They are used in various applications like heating, drying, sterilizing & baking.

**Construction :** All external cases are made of mild steel, with strong seamless welding & covered with a thick layer of stoved epoxy polyester paint. This provides a strong, highly screech & heat resistant surface for a long lasting attractive finish. Internal surfaces (including the doors) are manufactured from stainless steel, with great care in order to eliminate sharp edges. The double walled chamber is filled with high grade insulation to prevent heat loss. Elements are of the sheathed black type. They are put inside beads, placed at the bottom & in both the side ribs for uniform temperature. The door closes on to an asbestos-gasket. The shelves slide neatly into the fixed runners. The fixed ventilators are provided on both sides of the wall. The thermometer is provided on the top of the oven to check the temperature. The oven is mounted on four rubber feet to prevent slipping. The control panel houses a main On/Off switch, indicator lamp & temperature setting knob. The scale is calibrated in 5°C steps. Oven is controlled with capillary type thermostat. Provided with circulating fan for achieving uniform temperature throughout the chamber.

Particulars	Catalog No.
Oven, Hot Air, Memmert Type, Stainless Steel, Thermostatic with Fan, 300 x 300 x 300mm, 750 watts, 27 litre, 1 shelf	JA22030
Oven, Hot Air, Memmert Type, Stainless Steel, Thermostatic with Fan, 355 x 355 x 355mm, 800 watts, 45 litre, 2 shelves	JA22031
Oven, Hot Air, Memmert Type, Stainless Steel, Thermostatic with Fan, 405 x 405 x 405mm, 1000 watts, 65 litre, 2 shelves	JA22032
Oven, Hot Air, Memmert Type, Stainless Steel, Thermostatic with Fan, 455 x 455 x 455mm, 1500 watts, 95 litre, 2 shelves	JA22033
Oven, Hot Air, Memmert Type, Stainless Steel, Thermostatic with Fan, 455 x 455 x 605mm, 2000 watts, 125 litre, 2 shelves	JA22034
Oven, Hot Air, Memmert Type, Stainless Steel, Thermostatic with Fan, 605 x 605 x 605mm, 2000 watts, 220 litre, 2 shelves	JA22035
Oven, Hot Air, Memmert Type, Stainless Steel, Thermostatic with Fan, 605 x 605 x 910mm, 3000 watts, 330 litre, 3 shelves	JA22036

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.