



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# Oven, Hot Air, Memmert Type, Stainless Steel Outer and Inner, Digital Controller with Fan

## Product Image



## Description

---

Hot air ovens are suitable for temperature up to 250°C for chemicals, glassware in laboratories, research institutions, industries, hospitals & R & D centers. They are used in various applications like heating, drying, sterilizing & baking.

**Construction :** All external cases are made of 304 grade stainless steel, with strong seamless welding & covered with a thick layer of stoved epoxy polyester paint. This provide a strong, highly screech & heat resistant surface for a long lasting attractive finish. Internal surfaces (including the doors) are manufactured from stainless steel, with great care in order to eliminate sharp edges. The double walled chamber is filled with high grade insulation to prevent heat loss. Elements are of the sheathed black type. They are put inside beads, placed at the bottom & in both the side ribs for uniform temperature. The door closes on to an asbestos-gasket. The shelves slide neatly into the fixed runners. The fixed ventilators are provided on both sides of the wall. The oven is mounted on four rubber feet to prevent slipping. The control panel houses a main On/Off switch & indicator lamp. Oven is provided with digital temperature controller and indicator. Provided with circulating fan for achieving uniform temperature throughout the chamber.

Particulars	Catalog No.
Oven, Hot Air, Memmert Type, Stainless Steel Outer and Inner, Digital Controller with Fan, 355 x 355 x 355mm, 800 watts, 45 litre, 2 shelves	JA22091
Oven, Hot Air, Memmert Type, Stainless Steel Outer and Inner, Digital Controller with Fan, 405 x 405 x 405mm, 1000 watts, 65 litre, 2 shelves	JA22092
Oven, Hot Air, Memmert Type, Stainless Steel Outer and Inner, Digital Controller with Fan, 455 x 455 x 455mm, 1500 watts, 95 litre, 2 shelves	JA22093
Oven, Hot Air, Memmert Type, Stainless Steel Outer and Inner, Digital Controller with Fan, 455 x 455 x 605mm, 2000 watts, 125 litre, 2 shelves	JA22094
Oven, Hot Air, Memmert Type, Stainless Steel Outer and Inner, Digital Controller with Fan, 605 x 605 x 605mm, 2000 watts, 220 litre, 2 shelves	JA22095
Oven, Hot Air, Memmert Type, Stainless Steel Outer and Inner, Digital Controller with Fan, 605 x 605 x 910mm, 3000 watts, 330 litre, 3 shelves	JA22096

**Note:** Custom-made ovens to your specific requirements like size, material, control mechanism, configuration, shelves or special needs available on demand.

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of

product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.