



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

---

# Over Head Projector, Deluxe, ABS Body

## Product Image

---



## Description

---

**Optical System:**

Excellent contrast through 90mm single element uni-focal objective and anti-glare Fresnel lens which offers optimized brightness.

**Projection platform:**

250x250mm.

**Features:**

- Rust proof, shock proof, durable, all ABS body.
- Projector equipped with twin halogen lamps. Projection lamp with longest life, easy availability, low voltage and high intensity 2x24V/250W. System with a lamp quick-changer which can be easily operated from outside. Should a lamp fail during a presentation the spare lamp can be quickly utilized with simple turn of the knob. The projector does not have to be opened.
- Fine focusing with rack & pinion mechanism.
- Economy switch DIM/Bright.
- Whisper quiet cooling twin fan maintains low temperate on the stage.
- Easy to open working top, push the lock and open to working top.
- Safety interlock system, automatically cut off power of unit while replacing lamp.
- Overheating protection device.

**Specialties:**

- Ready for operation within seconds.
- Fold able projector arm.
- Rotating projection head 360°.
- Thermocol packing for safety during transportation and idle for repacking.

**Accessories:**

- Writing pack
- A-4 plain transparency 25nos
- 2 nos Glass fuse
- Dust cover

**Model****Catalog No.**

Over Head Projector, Deluxe, ABS Body    JM009300

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.