



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Over Head Projector, Regular, Sheet Metal

Product Image



Description

Optical System:

Excellent contrast through uni focal single element 90mm objective and clear fresnel lens.

Projection platform:

285 x 285mm.

Features:

- Sheet metal chassis.
- Projector equipped with twin halogen lamps. Projection lamp with longest life, easy availability, low voltage and high intensity 2x24V/250W. System with a lamp quick-changer which can be easily operated from outside. Should a lamp fail during a presentation the spare lamp can be quickly utilized with simple turn of the knob. The projector does not have to be opened.
- Fine focusing with rack & pinion mechanism.
- Economy switch DIM/Bright.
- Cooling throw cross flow fan maintains low temperatures on the stage.

Specialties:

- Ready for operation within seconds
- Foldable projector arm
- Thermocol packing for safety during transportation and idle for repacking.
- Rotating projection head 360°.

Accessories

- Writing pack
- 4 plain transparency 25nos
- 2 nos Glass fuse
- Dust cover.

Model**Catalog No.**

Over Head Projector, Regular, Sheet Metal JM009200

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.