



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Photocolorimeter, 8 Filters, Digital, Table Model

Product Image



Description

1 ml solution measurements.
Standard glass filters.
Highly stable & accurate.

Technical Specification:

Std. Glass Filter:	8
Mini Volume:	1ml
Display:	2½ Digit LED
Range:	400-700 nm
Output:	OD (0 to 1.99)
Resolution:	OD: 0.01
Accuracy:	0.5% FSI
Detector:	Selenium photocell
Light Source:	6.8V, 300mA
Power:	230V± 10% and in-built battery
Filters:	400, 420, 480, 500, 520, 540, 620, 680 nm

Accessories:

Set of 5 test tube.
Spare lamp.
Dust cover.
Manual.

Model	Catalog No.
Photocolorimeter, 8 Filters, Digital, Table Model	JA20280

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of

product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.