



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Photocolorimeter, Auto Zero, Digital, Table Model

Product Image



Description

Display both absorbance & %T models.

Range 400 to 700nm.

Fast & accurate operations.

Automatic zero calibration.

1ml. solution measurement.

Standard german glass filters.

Technical Specification:

Std. Glass Filter:	8
Mini Volume:	1ml
Display:	3 Digit, Bright Red 7 Segment LED
Range:	400-700 nm
Output:	(0 to 1.99), %T: 0 to 199
Resolution:	OD : 0.01, %T : 1%
Accuracy:	0.5% FSI
Detector:	Selenium Photocell/Photodiode
Light Source:	6.8v, 300mA
Power:	230V \pm 10%, 50 Hz. AC
Dimensions (l x b x h):	220x180x125mm (approx.)
Weight:	2 Kg (approx.)

Accessories:

Set of 5 test tube.

Spare lamp.

Dust cover.

Manual.

Model

Auto Zero, Photocolorimeter, Digital, Table Model

Catalog No.

JA20300

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.