



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Profile Projector, Industrial, 200mm Diameter

Product Image



Description

Body:

Compact Light weight table top profile projector with easy operations. 200mm diameter screen with 90° cross line and chart holders. Screen is graduated to 360° with vernier reading 6 minutes.

Focussing:

Focussing can be adjusted manually by hand knob.

Illumination:

Projection Light source with 24V/150W Halogen Lamp. Double Oblique Light source for surface illumination. Two adjustable dichroic reflector lamps 12V/100W each.

Objective:

High quality objective lenses.

Standard Magnification: 10X

Box: Supplied in card board packing.

Standard Features:

- Travel X-Y movement (Standard): 50x50mm
- Travel Z(Up and Down): 25mm (Under 10X)
- Travel Z(Up and Down): 50mm(Under 20X,50X & 100X)
- Micrometers (50mm Dia): 25mm(L.C 0.005)
- X-Y Bed Size :150x150mm

Optional Magnifications: 20X, 50X and 100X

Optical distortion below 0.15%. Cooling by built-in noiseless & vibration free fan.
Available in 110V & 220V through low voltage transformers. Supplied complete with operating instruction Manual.

Model	Catalog No.
Profile Projector, Industrial, 200mm Diameter	JM009900

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.