



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Resistance Box, Plastic

Product Image



Description

For accurate work. fitted in a plastic moulded box. Split brass contact blocks hold precision cut, interchangeable brass plugs having moulded black bakelite fluted tops. Coils of constantan wire, non-inductively wound, double silk covered; with resistances precisely adjusted and are mounted underneath the panel with double nut arrangement. Accuracy $\pm 0.1\%$.

Range (Ω)	Total(Ω)
1-50	110
1-100	210
1-500	1110
1-1000	2110
1-1500	3610
1-5000	11110
1-10000	21110

-

Resistance Box, Plastic, 1-50 Ohms	Catalog No. 101238 (A)
Resistance Box, Plastic, 1-100 Ohms	Catalog No. 101238 (B)
Resistance Box, Plastic, 1-500 Ohms	Catalog No. 101238 (C)
Resistance Box, Plastic, 1-1000 Ohms	Catalog No. 101238 (D)
Resistance Box, Plastic, 1-5000 Ohms	Catalog No. 101238 (E)
Resistance Box, Plastic, 1-10000 Ohms	Catalog No. 101238 (F)

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.