




Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Resistance Box, Plug Type

Product Image



Description

Resistance Box, Plug Type is of superior quality having heavy brass metal blocks are bound to bakelite plate by means of nuts and screws securing rigid fixation and eliminating any chance of contact error creeping due to loosening of plugs and lugs which are cut to fine taper and are interchangeable. Solder Joints are sealed after calibration. All Resistors are calibrated on imported Testing Bridge Accuracy $\pm 0.1\%$.

Available in Economy and Superior Types based on thickness of Brass Block.

Catalogue No	Particulars
---------------------	--------------------

JZ02700	Resistance Box Plug Type, 50 ohms, Superior Type
JZ02701	Resistance Box Plug Type, 100 ohms, Superior Type
JZ02702	Resistance Box Plug Type, 500 ohms, Superior Type
JZ02703	Resistance Box Plug Type, 1000 ohms, Superior Type
JZ02704	Resistance Box Plug Type, 50 ohms, Economy
JZ02705	Resistance Box Plug Type, 100 ohms, Economy
JZ02706	Resistance Box Plug Type, 500 ohms, Economy
JZ02707	Resistance Box Plug Type, 1000 ohms, Economy

A quality product from JAPSON ideal for use in School Laboratories in developing countries of Asia, Africa and South America.

Standard specifications for school laboratory use. Ideal mix of Quality and Economy.

Other configurations and superior quality available for specific use or for developed countries.

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.