



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# Resistance Box Decade Type

## Product Image



## Description

---

This decade resistance substitution box provides 1 ,2 3 or 4 decade ranges from 1 to 1000 ohm with a resolution of 10%. Each decade is selected by a rotary switch. Tapping points are provided across each range to allow the unit to be used as an accurate potential divider.

<b>Catoluge No</b>	<b>Particulars</b>
JZ02720	Resistance Box Decade Type, 0-1 ohms Single Dial
JZ02721	Resistance Box Decade Type, 0-10 ohms Double Dial
JZ02722	Resistance Box Decade Type, 0-100 ohms Triple Dial
JZ02723	Resistance Box Decade Type, 0-1000 ohms Four Dials

A quality product from JAPSON ideal for use in School Laboratories in developing countries of Asia, Africa and South America.

Standard specifications for school laboratory use. Ideal mix of Quality and Economy.

Other configurations and superior quality available for specific use or for developed countries.

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.