



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# Rheostats, Nichrome Type

## Product Image



## Description

Rheostat are used as series resistors or potentiometers. Open type slide wire type with a variety of resistance and current carrying capacity. Nichrome wire is used as resistance. Contact provided on metal chrome plated slider-rod to give rapid and smooth adjustment.

Three bell type terminals are provided. One at each end of the wire and the third at one end of the slider-rod thus the Rheostat can be used as potentiometer also. Resistance in ohms and current carrying capacities are marked on it. The end support are made of bakelite.

<b>Catoluge No</b>	<b>Particulars</b>
JZ02850	Rheostats 10 ohms Nichrome Type, Bell Terminals
JZ02851	Rheostats 20 ohms Nichrome Type, Bell Terminals
JZ02852	Rheostats 30 ohms Nichrome Type, Bell Terminals
JZ02853	Rheostats 50 ohms Nichrome Type, Bell Terminals
JZ02854	Rheostats 100 ohms Nichrome Type, Bell Terminals

A quality product from JAPSON ideal for use in School Laboratories in developing countries of Asia, Africa and South America.

Standard specifications for school laboratory use. Ideal mix of Quality and Economy. Other configurations and superior quality available for specific use or for developed countries.

## **Disclaimer**

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.