



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

---

# Rockwell Hardness Tester, Electronic

## Product Image

---



## Description

---

Rockwell Testing Machines are highly reliable, accurate and durable hardness testing machines. These machines are used for determining the hardness of ferrous and non-ferrous metals with high reliability and accuracy.

**Rockwell Scale:** HRA, HRB, HRC

<b>Preliminary Test Force:</b>	10Kg (98.07N)
<b>All Testing Force:</b>	60Kgf (588.4N), 100 Kgf (980.7N), 150Kgf (1471N)
<b>Hardness Indication:</b>	Analogue Display
<b>Hardness Resolution:</b>	0.5 HR
<b>Dwell Time:</b>	Adjustable 1-60 S
<b>Auto Hardness Conversion:</b>	HRA, HRB, HRC, HRD, HRF, HV, HK, HBW HR15N, HR30N, HR45N, HR15T, HR30T, HR45T
<b>Max. Height of Specimen:</b>	175 mm
<b>Instrument throat:</b>	165 mm
<b>Dimensions (L x W x H):</b>	520x215x700mm
<b>Packing Dimensions:</b>	630x440x960mm
<b>Gross / Net Weight:</b>	120 / 90Kg
<b>Power Supply:</b>	AC220V / 50Hz; 110V / 60Hz
<b>Accuracy:</b>	Conform to GB/T230.2; ASTM E-18; ISO6508

<b>Model</b>	<b>Catalog No.</b>
Rockwell Hardness Tester, Electronic	7005 RHT-E

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.