



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Spot Reflecting Galvanometer

Product Image



Description

This galvanometers has a built in lamp and scale arrangement based in a sturdy bakelite case with lock/unlock knob at the top and on/off switch. 4mm color coded socket terminal is

provided for input and sensitivity adjustment knob at the front. Operates on 220-240V AC 50/60Hz.

Time period: 2 second approx.

Damping Resistance: 125Ω or 500Ω

Sensitivity: 5 to 6μA FSD

Catalog No.	Model
JP11450	Spot Reflecting Galvanometer

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.