



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

# Spot Reflecting Galvanometer

## Product Image



## Description

This galvanometers has a built in lamp and scale arrangement based in a sturdy bakelite case with lock/unlock knob at the top and on/off switch. 4mm color coded socket terminal is

provided for input and sensitivity adjustment knob at the front. Operates on 220-240V AC 50/60Hz.

**Time period:** 2 second approx.

**Damping Resistance:** 125 $\Omega$  or 500 $\Omega$

**Sensitivity:** 5 to 6 $\mu$ A FSD

Catalog No.	Model
JP11450	Spot Reflecting Galvanometer

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.