



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Tachometer

Product Image



Description

Features:

--

Product Introduction

Tachometer machinery industry is one of the essential instruments for measuring motor speed, line speed or frequency. Precision measurement can impeller blades, the drum, the rotational speed of the spindle shaft. Widely used in motors, fans, washing, textile, automobile, aircraft, ships and other industries.

Specifications

Display	5 Digit LCD Display
Unit	rpm
Measuring Range	2.5-99999rpm
Resolution	0.1rpm(2.5-999.9rpm) 1rpm(1000-99999rpm)
Accuracy	(0.1%n+5d)rpm;(2.5-999.9rpm) (1%n+5d)rpm;(1000-99999rpm)
Laser Power	CLASS II 2-5mW
Sampling Rate	1 Time/Second
Measuring Distance	50-500mm
Time Base	Quartz Crystal
Auto Power Off	1 Minute without Any Operation
Operating Environment	0°-50°C; 32~122°F; 10%~90%RH
Storage Environment	-10°-80°C; -14~176°F; 10%-75%RH
Unit Size	55.7*29.9*127mm
Power	2*1.5V AAA Batteries
MAX/ MIN/ AVG/ LAST Value	✓
Low Battery Indication	✓
LCD Backlight	✓
Memory	✓
Weight	106g

--

Tachometer

Catalogue No. **101433**

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.