



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Ultrasonic Cleaners

Product Image



Description

Catalog No : 100138

Ultrasonic Cleaners - Model 350

Tank Capacity : 2.0L, 2.5L, 3.5L, 4.5L, 5L, 6L, 8 L, 11 L & 24 L.

TECHNICAL SPECIFICATIONS

✓ Ultrasonic Frequency	40,000 Hz
✓ Material	Stainless Steel SUS304
✓ Tank Capacity	2.0L, 3.5L & 4.5L
✓ Timer	1 -30minutes,
✓ Digital timer	Power Supply AC 100 — 120V, 50 / 60Hz AC 220 — 240V, 50 / 60 Hz
✓ Ultrasonic Power	240W
✓ Heating Power	200 W, Digital Heating
✓ Unit Size	325 x 265 x 280 mm (LxWx H)
✓ Tank Size	300 x 240 x 150 mm (L xW x H)
✓ Package Size	430 x 365 x 420 mm (LxWx H)
✓ N.W.	6.0 kg
✓ G .VV.	7.0 kg

ACCESSORIES

- ✓ Stainless steel tank has resistance to wear and long work life.
- ✓ With digital timer & heater control.
- ✓ With Stainless steel basket
- ✓ Use just tap water, or industrial alcohol and solvent cleaner for more higher cleaning requirement
- ✓ Industrial control chip micro controller flexible circuit boards control
- ✓ More secure & stable
- ✓ Temperature tunable from 20°C to 80°C.

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.