



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Ultrasonic Thickness Gauge

Product Image



Description

Features:

--

Specifications

	RT-100	RT-130
Measuring Range	1.2-225mm(Steel),	1.0-300MM(Steel)
Accuracy	±(1%H+0.1)mm	±(1%H+0.1)mm
Resolution	0.1mm,	0.01mm
Sound Velocity Range	1000-9999m/s	1000-9999m/s
Working Frequency	5MHz	5MHz
Minimum Limit for Tube Measuring	20*3mm(Steel),	10mm Probe: 20*3mm(Steel)
Auto Calibration to Assure The Accuracy	√	
Data Store/Recall /Delete Function	√	
Sound Velocity Measurement	√	
Low Battery indication	√	
Auto Power Off	√	
LCD Backlight Display	√	
Unit Size	80*38*150mm	
Standard Quantity Per Carton	12PCS	
Power Supply	3*1.5V AAA Batteries	

Ultrasonic Thickness Gauge

Catalogue No. **101434**

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.